

With Good Reason

Pressure Reducing Valves

from Berluto



Features

- pre-pressure relief
- suited for water, liquids, air and gases
- valve body in red bronze
- internal parts made from brass or stainless steel; seawater version is optionally available
- seals in NBR; EPDM seals are optionally available
- double-sided manometer connections
- face-to-face dimensions and flanges according to DIN EN 1092 PN 16 or PN 25 (optionally ANSI B 16.5)
- kvs-value 210 m³/h
- various outlet pressure ranges:
1,5 - 6 bar
3,0 - 10 bar
0,5 - 4 bar
0,5 - 9 bar

now up to
DN 150



Made
in
Germany

With Good Reason

Pressure Reducing Valves from Berluto



PN bar	p ₂ bar	Nominal Size	kvs m ³ /h	Design	Flange DRV - Type	for Seawater
Diaphragm pressure reducer for standard & wide range pressure						
16	1,5 - 6	DN80 - DN150	60 - 210	Diaphragm	DRV 602/-6	DRV 602 SW*
16	0,5 - 4	DN80 - DN150	60 - 210	Diaphragm	DRV 672	
16	3 - 10	DN80 - DN150	60 - 210	Diaphragm	DRV 608	
16	0,5 - 9	DN80 - DN150	60 - 210	Diaphragm	DRV 678	DRV 678 SW*
Pressure reducer with high pressure piston						
25	4 - 12	DN80-DN100	60 - 70	Piston	DRV 624	

* further pressure ranges on request

Features

Our large flange pressure reducers of series DRV 600 provide extended flow capacities and are primarily used for the pressure reduction of (drinking) water or other neutral liquids.

With adequate flow rate requirements these valves may also be used for compressed air, nitrogen or other neutral, non-combustible gases. All types of series 600 are pressure-relieved, i.e. fluctuating inlet pressures will not affect the outlet pressure.

As standard, the flange connections correspond to DIN EN 1092/PN 16 or PN 25, ANSI- or JIS-flanges are available on request.

Type DRV 602-6 is specially designed for drinking water. The processed metals comply with the UBA positive list and all seals are KTW- and W270-certified.

As a special feature it should be noted that this type is also offered as seawater-resistant version.



Master Distributor In China
QUKO Int'l Development Limited
Unit B, 17/F, EGL Tower, 83 Hung To Road, Kwun Tong,
Kowloon, Hong Kong, China
Tel: (852) 2344 0201 Fax: (852) 2343 6078
Email: sales@qukointl.com Website: www.qukointl.com